

Powered Direct Connect 23m Cable Kit

PRODUCT MANUAL

Items 3660DP & 3927C75

KIT CONTENTS

- A. 90-264V AC Adapter and the USA to Europe adapter included
3660DP: 6V, 1.25A
3927C75: 12V, 0.7A
- B. Direct Connect Power and Data Adapter
- C. 23m 6-conductor extension cable

Spectrum[®]
Technologies, Inc.

3600 Thayer Court
Aurora, IL 60504
(800) 248-8873 or (815) 436-4440
Fax (815) 436-4460
E-Mail: info@specmeters.com
www.specmeters.com


POWERED DIRECT CONNECT 23M CABLE

3660DP (for Weather Station) and 3927C75 (for Retriever)

Follow these steps to connect the powered 23m cable to your Weather Station or Retriever.

KIT CONTENTS

- A. AC Adapter and USA-to-Europe adapter
3660DP: 6V, 1.25A
3927C75: 12V, 0.7A
- B. Direct Connect Power and Data Adapter
- C. 23m 6-conductor extension cable



INSTRUCTIONS

1 Connect 23m cable end without the gland (cord grip) to the adapter.

2 Connect 9-pin female end of the adapter to your PC, either directly to a serial port or using a USB-to-Serial adapter (3661USB).


3 Connect the power supply to the A/C adapter.

4 Remove the existing gland from the rightmost position of the Weather Station or Retriever.

3660DP NOTICE:

Remove all alkaline batteries from the Weather Station before plugging the cable into the station.

5 Insert the cable into the Station or Retriever through the open gland hole and plug it into the AUX port. Screw the gland (cord grip) into the hole to secure the cable and seal the opening.



(Retriever is shown here for illustration.)

