

Powered Direct Connect 75 FT Cable Kit

PRODUCT MANUAL

Items 3660DP & 3927C75

Spectrum[®]
Technologies, Inc.

3600 Thayer Court
Aurora, IL 60504
(800) 248-8873 or (815) 436-4440
Fax (815) 436-4460
E-Mail: info@specmeters.com
www.specmeters.com

POWERED DIRECT CONNECT 75 FT CABLE

3660DP (for Weather Station) and 3927C75 (for Retriever)

Follow these steps to connect the powered 75-ft cable to your Weather


KIT CONTENTS

- A. AC/DC power supply
3660DP: 6V, 1.25A
3927C75: 12V, 0.7A
- B. Direct Connect Power and Data Adapter
- C. 75-ft 6-conductor



INSTRUCTIONS

1 Connect 75 ft cable end without the gland




2 Connect 9-pin female end of the adapter to your PC, either directly to a serial port or using a USB-

3 Connect the power

(Retriever is shown here for illustration.)

4 Remove the existing gland from the rightmost position of the Weather Station or Retriever.



3660DP NOTICE:

Remove all alkaline batteries from the Weather Station before plugging the cable into the

5 Insert the cable into the Station or Retriever through the open gland hole and plug it into the AUX port. Screw the gland (cord grip) into the